

FREE-STANDING RACKS


PREMIUM HOUSING RSB



RSB-42-80/100-3

The PREMIUM Housing RSB rack series is designed for server housing and co-location centers. All types of active or passive 19" equipment can be housed inside.





MAIN ADVANTAGES

- > Flexible server-housing rack for collocation and housing data centers
- 2, 3 and 4 individual compartments
- Unmatched 86% door perforation ratio decreases server fan power consumption
- Installable as standalone or in rows with other racks
- Individual cable guides for cable management
- Separation frame for each compartment





DESCRIPTION

- Height: 42, 45, 48U (total useful height = 42/45/48 minus number of compartments)
- Width: 600, 800 mm
- Depth: 1000 and 1200 mm

Construction

- 1.5 & 2.0 mm sheet steel
- 2-4 compartments; other combinations upon request

Load rating

- 1500 kg maximum load rating per frame
- Load rating 500 kg per 19" compartments; 100 kg per shelf

IP rating

• IP20

• Standard RAL 7035 and 9005

Front and rear doors

- Vented door—perforation rate 86%
- Swivel handle lock—DIN profile, universal key 333, single point
- Door opening angle 180°
- Easy re-hanging to open on right or left

Side panels

• Removable with locks

Cable entries

- Top and bottom
- All cable entries covered with removable blank panels


19" Vertical extrusions


- 2 pairs of sliding 19" vertical L-type (600mm) or P-type (800mm) extrusions for 2 and 3 compartments
- C-type extrusions for RSB width 800 mm (4 compartments)

Other

- Installable in blocks with DP-DR-UNI (ordered separately)
- GND/earthing kit included
- Individual cabling for each compartment (ordered separately)
- Air separation frame for all compartments (ordered separately)

PREMIUM Housing RSB Racks





RSB-42-80/100-3

STANDARD CONFIGURATION (short Code only) *		OPTIONS		
1	Server housing rack frame	7	Set of individual cable guiding	
2	3 pieces of high-load shelf	8	Separation frame for each compartment	
3	2 removable side panels with locks			
4	6 pieces of vented doors with swivel handle lock			
5	Removable Z-design top plate with cable entry openings			
6	2 pairs of 19" vertical P-type extrusions for each compartment			
•	GND/earthing kit			
•	28 mounting kits			

^{*} Valid for RSB racks with 3 compartments.

Technical data and dimensions

Code	H (in U) Load ratin (kg)	Load rating	Dimensions (mm)			Dimensions incl. packing (mm)			Gross weight (kg)	
Code			Н*	W	D	Useful depth	н	W	D	(compartments—2/3/4)
RSB-42-60/100	42	1500	1978	600	1000	931	2160	640	1040	137/158/181
RSB-45-60/100	45	1500	2 111	600	1000	931	2 290	640	1040	144/165/190
RSB-48-60/100	48	1500	2 245	600	1000	931	2 430	640	1040	151/173/198
RSB-42-60/120	42	1500	1978	600	1200	1131	2160	640	1240	165/188/219
RSB-45-60/120	45	1500	2 111	600	1200	1131	2 290	640	1240	174/196/230
RSB-48-60/120	48	1500	2 245	600	1200	1131	2 430	640	1240	184/205/240
RSB-42-80/100	42	1500	1978	800	1000	931	2160	840	1040	169/194/224
RSB-45-80/100	45	1500	2 111	800	1000	931	2 290	840	1040	175/202/231
RSB-48-80/100	48	1500	2 245	800	1000	931	2 430	840	1040	179/206/233
RSB-42-80/120	42	1500	1978	800	1200	1131	2160	840	1240	205/234/261
RSB-45-80/120	45	1500	2 111	800	1200	1131	2 290	840	1240	211/237/276
RSB-48-80/120	48	1500	2 245	800	1200	1131	2 430	840	1240	220/248/282

^{*} Height in mm without feet; for feet add 16-45 mm.

PREMIUM Housing RSB Racks—ordering and shipping information

Configure the rack that meets your requirements. The ordering matrix below will help you create a Code. As soon as you have the Code, please contact your CONTEG products distributor. Please note that all RSB racks are delivered fully assembled and palletized.

FOLLOW THE STEPS TO SET UP THE DESIRED RSB RACK CODE



1. HEIGHT *			
Code	Height (in U)	External height (mm)	
42	42	1978	
45	45	2111	
48	48	2 2 4 5	

2. WIDTH			
Code	Width (mm)		
60	600		
80	800		

3. DEPTH			
Code	Depth (mm)		
100	1000		
120	1200		

^{*} Height in mm without feet.

4. NUMBER OF COMPARTMENTS			
Code Options			
2	2 compartments		
3	3 compartments		
4	4 compartments		
4	4 compartments		

5. COLOR			
Code	Note		
В	RAL 7035 (light gray)		
н	RAL 9005 (black)		

ACCESSORIES			
Code	Description		
RSB-CM-xx ¹	Set for individual cable guiding of RSB racks, top or bottom cable entry		
DP-RSB-CW-y²-xx¹	Set of air separation frames for RSB racks		

¹Substitute xx with height of RSB rack

Recommended accessories





Managed PDU

RAMOS Ultra

²Substitute y with number of compartments

